

SHAKER ACCESSORIES

PM-MS ADAPTOR

MS-ST STINGER SET


DynaLabs

The PM-MS converter (PM-MA) and stinger set enable the conversion of a Permanent Magnet shaker into a Modal Shaker.



Modal Shakers are attached to the structure using a stinger, which transfers force from the shaker to the structure, preventing direct interaction between the two. Each modal shaker package includes a stinger set with stinger rods of 2mm, 2.4mm, and 3.2mm lengths, along with collets and nuts. The Permanent Magnet shaker can be converted into a Modal Shaker using the PM-MS adaptor and stinger set, with different size adaptors used for each shaker.

MS-ST Stinger Set:



Collet : 4 pc (0.75mm/1.6mm/2.4mm/3.2mm)
Stainless Rod : 3 pc ($\varnothing 2\text{mm} + \varnothing 2.4\text{mm} + \varnothing 3.2\text{mm} = \text{L}300 \text{ mm} (+10)$)

PM-MS Adapter:

Different size adapter is used for each shaker.



20N



100N



250N+440N



DYNALABS MUHENDISLIK LTD STI

Ostim OSB Mah. 100 Yil Bulvarı Ostim
No:55B/11 Yenimahalle 06374 Ankara
TURKEY

Phone: +90 312 386 21 89

Mail: dynalabs@dynalabs.com.tr

Web: www.dynalabs.com.tr